



# HF-Performer III for TL-D lamps

## HF-P 3/418 TL-D III 220-240V 50/60Hz IDC

HF-Performer III TLD is a sustainable, slim and high-frequency electronic ballast for TL-D fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2).

### Product data


Operating and Electrical		T-Case maximum (max.)	80 °C
Input Voltage	220 to 240 V	Mechanical and Housing	
Line Frequency	50 to 60 Hz	Housing	L 280x40x28
Input frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Inrush current width	0.25 ms	Net Weight (Piece)	0.250 kg
Power Factor (Fraction)	0.99	Approval and Application	
Inrush current peak (max.)	24 A	Energy efficiency index	A2 BAT
Number of products on MCB (16 A type B) (nom.)	28	Safety standard	IEC 61347-2-3
Wiring		Environmental standard	ISO 14001
Connector type input terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Approval marks	CE marking ENEC certificate VDE-EMV certificate
Connector type output terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	CE mark	Yes
		Ambient temperature range	-25°C to 60°C
Temperature		Product Data	
T-case lifetime (nom.)	80 °C	Order product name	HF-P 3/418 TL-D III 220-240V 50/60Hz IDC
		Full product name	HF-P 3/418 TL-D III 220-240V 50/60Hz IDC
		Full EOC	872790091162600

## HF-Performer III for TL-D lamps

Order code	913713031466
Material no. (12 NC)	913713031466
Local order code	HFP3418TLDIII
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500999627

Numerator – packs per outer box	10
EAN/UPC – Case	8727900911626

### Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-P 3/418 TL-D III 220-240V 50/60Hz IDC	4.2 mm	28.0 mm	280.0 mm	265.0 mm	40.0 mm

