



HF-Performer III for TL5 lamps

HF-P 2 24/39 TL5 III 220-240V 50/60Hz

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

Product data


Operating and Electrical		T-Case maximum (max.)	80 °C
Input Voltage	220 to 240 V	Mechanical and Housing	
Line Frequency	50 to 60 Hz	Housing	L 360x30x21
Input frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Inrush current width	0.30 ms	Net Weight (Piece)	0.250 kg
Inrush current peak (max.)	24 A	Approval and Application	
Number of products on MCB (16 A type B) (nom.)	20	Energy efficiency index	A2 BAT
Wiring		Safety standard	IEC 61347-2-3
Connector type input terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Environmental standard	ISO 14001
Connector type output terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Approval marks	CE marking ENEC certificate VDE-EMV certificate
Temperature		CE mark	Yes
T-case lifetime (nom.)	80 °C	Ambient temperature range	-25°C to 60°C
Product Data		Order product name	HF-P 2 24/39 TL5 III 220-240V 50/60Hz
		Full product name	HF-P 2 24/39 TL5 III 220-240V 50/60Hz
		Full EOC	872790095226100

HF-Performer III for TL5 lamps

Order code	913713034166
Material no. (12 NC)	913713034166
Local order code	HFP224-39TLEIIL
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900952261

Numerator – packs per outer box	12
EAN/UPC – Case	8727900952278

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-P 2 24/39 TL5 III 220-240V 50/60Hz	4.2 mm	21.0 mm	360.0 mm	350.0 mm	30.0 mm

