PHILIPS

Univeral Socket

Switches & Sockets

Smart+

Matte Black

2 Module

913713641501



Switch to a classy interior

Philips Smart+ Matt Black range adds premium décor to your wall with a mix blend of Glossy & Matt finish.

Easy to use
- Shrouded terminals with captive screws
- Front insertion & front removal
- Low insert height
- Convenient grip for plug

Safe to use
- FR Grade Polycarbonate Material
- Safe to use even with wet hands

Longer lifetime
- Brass terminals
- Brass screw

Choose for a sustainable solution
- RoHS compliant

Highlights

Shrouded terminals with captive screws
Shrouded terminals for easy installation. Screws wont come out during wire fixing.

Front insertion & front removal
Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Low insert height
Low insert height so that you get more space for wiring inside the installed box.

Convenient grip for plug
Convenient gripping inside the socket for the inserted plug for better connectivity.

FR Grade Polycarbonate Material
Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

Safe to use even with wet hands
No seepage of water due to precision & covered design.

Brass terminals
Brass terminal for connection for longer, uninterrupted life.

Brass screw
Brass screw for longer, carefree operations.

RoHS compliant
All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

Specifications

Design and finishing
- Color: black
- Material: PC
- Module/Gang: 2 Module
- Socket/connector Type: Universal
- Product Range: Smart+
- Minimum Installation Box Depth: 50 mm

Durability
- Number of Operation Cycles: 5,000

Interactivity
- Current (A): 13A

Other characteristics
- Installation Type: Fast Installation
- Indicator Type: No Indicator

Power
- Electrical Load Type: Resistive load

Power consumption
- Voltage: 240 V

Product dimensions & weight
- Length: 5 cm
- Width: 4.5 cm
- Depth: 3.5 cm

Service
- Warranty: 2 year(s)

Technical specifications
- Frequency: 50 Hz

Packaging dimensions and weight
- EAN/UPC - product: 8718696665237
- Net weight: 0.031 kg
- Gross weight: 0.031 kg
- Height: 3.450 cm
- Length: 5.000 cm
- Width: 4.500 cm
- Material number (12NC): 913713641501

Issue date: 2023-11-08
Version: 0.277

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com