

# PHILIPS

## 3 Pin socket

### Switches & Sockets

Smart+

Matte Black

2 Module

25A

913713641901



## Switch to a classy interior

Philips Smart+ Matt Black range adds premium décor to your wall with a mix blend of Glossy & Matt finish.

### Easy to use

- Shrouded terminals with captive screws
- Front insertion & front removal
- Low insert height
- Dual shutter technology
- Convenient grip for plug

### Safe to use

- FR Grade Polycarbonate Material
- Safe to use even with wet hands

### Longer lifetime

- Brass terminals
- Brass screw

### Safe for kids

- Dual shutter technology

### Choose for a sustainable solution

- RoHS compliant

# Highlights

## **Shrouded terminals with captive screws**

Shrouded terminals for easy installation. Screws won't come out during wire fixing.

## **Front insertion & front removal**

Smart way to preserve your designer walls, remove your switch/socket without dismantling the plates. Inserts can be fixed or removed from front.

## **Low insert height**

Low insert height so that you get more space for wiring inside the installed box.

## **Dual shutter technology**

Even 2 Pin Plug can be inserted easily without the help of any screw driver/pencil to hold the top shutter.

## **Convenient grip for plug**

Convenient gripping inside the socket for the inserted plug for better connectivity.

## **FR Grade Polycarbonate Material**

Best quality polycarbonate material which doesn't catch fire easily. Material also clears the Glow Wire Test @ 850 Degree Celsius.

## **Safe to use even with wet hands**

No seepage of water due to precision & covered design.

## **Brass terminals**

Brass terminal for connection for longer, uninterrupted life.

## **Brass screw**

Brass screw for longer, carefree operations.

## **Dual shutter technology**

Separate in-built shutter for L/N pin & earth pin make easy fitment even for 2 pin plug, also makes it safer even when kids are around. Separate shutter prevents from accidental finger insertion.

## **RoHS compliant**

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

# Specifications

## Design and finishing

- Color: black
- Material: PC
- Module/Gang: 2 Module
- Socket/connector Type: Combination Socket
- Product Range: Smart+
- Minimum Installation Box Depth: 50 mm

## Durability

- Number of Operation Cycles: 5,000

## Interactivity

- Current (A): 25A

## Other characteristics

- Installation Type: Fast Installation
- Indicator Type: No Indicator

## Power

- Electrical Load Type: Resistive load

## Power consumption

- Voltage: 240 V

## Product dimensions & weight

- Length: 5 cm
- Width: 4.5 cm
- Depth: 4.5 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 8718696665329
- Net weight: 0.034 kg
- Gross weight: 0.035 kg
- Height: 5.120 cm
- Length: 5.000 cm
- Width: 4.500 cm
- Material number (12NC): 913713641901



Issue date: 2023-11-08  
Version: 0.391

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)