

# PHILIPS

Stabilizer

Circuit Breakers

White

1.5 Ton

913713874001



## Intelligent products for protection of your appliances

Philips Stabilizer range with smart delay technology, that safeguards your appliances from voltage fluctuations.

### Easy to use

- Gloss finish

### Safe to use

- FR Grade Polycarbonate Material
- Smart Start
- Cut-Off protection

### Durability

- Brass terminal for screw tightening

### Convenience

- DGR Compatible

# Highlights

## Gloss finish

Glossy white finish which flushes with the wall and also easy to clean.

## FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

## Smart Start

Intelligent start delay for overload protection.

## DGR Compatible

Supports generator supply.

## Cut-Off protection

Prevents from Voltage fluctuation.

## Brass terminal for screw tightening

brass terminal for screw tightening.

# Specifications

## Design and finishing

- Material: metal

## Interactivity

- Current (A): 12

## Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: LED

## Power consumption

- Voltage: 170-270 V

## Product dimensions and weight

- Height: 8 cm
- Length: 22 cm
- Width: 15.3 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Frequency: 50 Hz



Issue date: 2023-11-08  
Version: 0.265

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)