

# PHILIPS

## 1 Way Switch

### Switches & Sockets

Metallica

Grey

1 Module

10A

913713969801



# Create impression with a Metallic touch

Add décor to your home with Philips Metallica range.

#### Easy to use

- Front insertion & front removal
- Glossy finish
- Low insert height

#### Safe to use

- FR Grade Polycarbonate Material
- ISI mark
- Safe to use even with wet hands
- Spark shield

#### Longer lifetime

- Brass terminals
- Brass screw
- Silver based contact rivet
- Superior material quality

#### Choose for a sustainable solution

- RoHS compliant

#### Durability

- 1 Lac operations

# Highlights

**Front insertion & front removal**

Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

**Glossy finish**

Glossy external finish for easy to clean and long lasting finish.

**Low insert height**

Low insert height so that you get more space for wiring inside the installed box.

**FR Grade Polycarbonate Material**

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

**ISI mark**

ISI mark (tested as per indian standard IS3854).

**Safe to use even with wet hands**

No seepage of water due to precision & covered design.

**Spark shield**

No visible spark during the switch operation.

**Brass terminals**

Brass terminal for connection for longer, uninterrupted life.

**Brass screw**

Brass screw for longer, carefree operations.

**Silver based contact rivet**

Silver based contact rivet for better connectivity and long life.

**Superior material quality**

Phosphorus bronze internal wire which last long and makes the product long lasting.

**RoHS compliant**

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

**1 Lac operations**

Tested upto 1 Lac on and off operations for ultra long life.

# Specifications

## Design and finishing

- Color: Grey
- Material: Metal, Plastic
- Module/Gang: 1 Module
- Product Range: Metallica
- Minimum Installation Box Depth: 5 cm

## Durability

- Number of Operation Cycles: 40,000

## Interactivity

- Current (A): 10

## Miscellaneous

- Approval Marks: BIS Certificate

## Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: No Indicator

## Power

- Electrical Load Type: Resistive load

## Power consumption

- Voltage: 240 V

## Product dimensions and weight

- Length: 5 cm
- Width: 2.25 cm
- Depth: 3.35 cm

## Rated values

- Fluorescent Lamp Current: 10 AX

## Service

- Warranty: 5 year(s)

## Technical specifications

- Frequency: 50 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 8718699652227
- Net weight: 0.02 kg
- Gross weight: 0.02 kg
- Height: 3.4 cm
- Length: 5 cm
- Width: 2.3 cm
- Material number (12NC): 913713969801



Issue date: 2024-02-04  
Version: 0.33

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)