PHILIPS

1 Way Switch with Indicator

Switches & Sockets

Metallica

Grey

1 Module

10A

913713969901



Create impression with a Metallic touch

Add décor to your home with Philips Metallica range.

Easy to use
- Front insertion & front removal
- Glossy finish
- Indicator to display on/off
- Low insert height

Safe to use
- FR Grade Polycarbonate Material
- ISI mark
- Safe to use even with wet hands
- Spark shield

Longer lifetime
- Brass terminals
- Brass screw
- Silver based contact rivet
- Superior material quality

Choose for a sustainable solution
- RoHS compliant

Durability
- Neon bulb for Indication

Highlights

Front insertion & front removal
Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Glossy finish
Glossy external finish for easy to clean and long lasting finish.

Indicator to display on/off
Red marking provided on the top for 16A & above rated switch for convenience during installation.

Low insert height
Low insert height so that you get more space for wiring inside the installed box.

FR Grade Polycarbonate Material
Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

ISI mark
ISI mark (tested as per indian standard IS3854).

Safe to use even with wet hands
No seepage of water due to precision & covered design.

Spark shield
No visible spark during the switch operation.

Brass terminals
Brass terminal for connection for longer, uninterrupted life.

Brass screw
Brass screw for longer, carefree operations.

Silver based contact rivet
Silver based contact rivet for better connectivity and long life.

Superior material quality
Phosphorus bronze internal wire which last long and makes the product long lasting.

RoHS compliant
All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

Neon bulb for Indication
Better brightness with Neon indication and longer life.

Specifications

Design and finishing
- Color: grey
- Material: metal/plastic
- Module/Gang: 1 Module
- Product Range: Metallica
- Minimum Installation Box Depth: 5 cm

Durability
- Number of Operation Cycles: 40,000

Interactivity
- Current (A): 10

Miscellaneous
- Approval Marks: BIS Certificate

Other characteristics
- Installation Type: Screwed Installation
- Indicator Type: Flourescent

Packaging dimensions and weight
- Net weight: 0.016 kg

Power
- Electrical Load Type: Resistive load

Power consumption
- Voltage: 240 V

Product dimensions & weight
- Length: 5 cm
- Width: 2.25 cm
- Depth: 3.35 cm

Rated values
- Fluorescent Lamp Current: 10 AX

Service
- Warranty: 2 year(s)

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699652258
- Gross weight: 0.017 g
- Height: 3.350
- Length: 5.000
- Width: 2.250
- Material number (12NC): 913713969901

Issue date: 2023-11-08
Version: 0.30

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com