

# PHILIPS

## DP Switch

### Switches & Sockets

Metallica

Grey

2 Module

20A

913713973201



# Create impression with a Metallic touch

Add décor to your home with Philips Metallica range.

#### Easy to use

- Shrouded terminals with captive screws
- Front insertion & front removal
- Glossy finish
- Indicator to display on/off
- Easy installation

#### Safe to use

- FR Grade Polycarbonate Material
- ISI mark
- Safe to use even with wet hands

#### Longer lifetime

- Brass terminals
- Brass screw
- Silver based contact rivet

#### Choose for a sustainable solution

- RoHS compliant

# Highlights

**Shrouded terminals with captive screws**

Shrouded terminals for easy installation. Screws won't come out during wire fixing.

**Front insertion & front removal**

Smart way to preserve your designer walls, remove your switch/socket without dismantling the plates. Inserts can be fixed or removed from front.

**Glossy finish**

Glossy external finish for easy to clean and long lasting finish.

**Indicator to display on/off**

Red marking provided on the top for 16A & above rated switch for convenience during installation.

**Easy installation**

Slot for Horizontal and vertical mounting/Hanging.

**FR Grade Polycarbonate Material**

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

**ISI mark**

ISI mark (tested as per Indian standard IS3854).

**Safe to use even with wet hands**

No seepage of water due to precision & covered design.

**Brass terminals**

Brass terminal for connection for longer, uninterrupted life.

**Brass screw**

Brass screw for longer, carefree operations.

**Silver based contact rivet**

Silver based contact rivet for better connectivity and long life.

**RoHS compliant**

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

# Specifications

## Design and finishing

- Color: grey
- Material: metal/plastic
- Module/Gang: 2 Module
- Product Range: Metallica
- Minimum Installation Box Depth: 5 cm

## Durability

- Number of Operation Cycles: 10,000

## Interactivity

- Current (A): 20

## Miscellaneous

- Approval Marks: BIS Certificate

## Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: Flourescent

## Packaging dimensions and weight

- Net weight: 0.047 kg

## Power

- Electrical Load Type: Resistive load

## Power consumption

- Voltage: 240 V

## Product dimensions & weight

- Length: 5 cm
- Width: 4.5 cm
- Depth: 5.2 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 8718699653248
- Gross weight: 0.048 g
- Height: 5.200
- Length: 5.000
- Width: 4.500
- Material number (12NC): 913713973201



Issue date: 2023-11-08  
Version: 0.30

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)