



SunStay

BRP710 LED20 WW MR 12V 28PO PDIM50 Solar

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

Product data

General Information	
Driver included	Yes
Value ladder	Specification
Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>70
Light source color	Warm white
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	13.6 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Poly crystalline
Panel voltage	17 Vmp, 21 Voc V
Panel peak wattage	28 W
Charge controller type	MPPT
Grid connection type	Off grid

Controls and Dimming	
Dimmable	Yes
Configurability	Factory Configurable
Solar dimming profile	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
Mechanical and Housing	
Housing Material	Aluminium pressure die cast
Housing Color	Gray
Overall length	684 mm
Overall width	369 mm
Overall height	156 mm
Dimensions (Height x Width x Depth)	156 x 369 x 684 mm
Battery location	Inside Luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	UV stabilized Polycarbonate cover
Net Weight (Piece)	9.500 kg
Approval and Application	
Ambient temperature range	0 to +35 °C

Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)
Application Conditions	
Ambient temperature range for charging	0 °C to +45 °C
Ambient temperature range for discharging (when light is on)	-20 °C to +35 °C
Product Data	
Order product name	BRP710 LED20 WW MR 12V 28PO PDIM50
	Solar

Full product name	BRP710 LED20 WW MR 12V 28PO PDIM50
	Solar
Full product code	871016335456900
Order code	919515812967
Material Nr. (12NC)	919515812967
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163354569
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163354569

Dimensional drawing

