



# Halogen non-reflector

## BRL 7027 50W 12V 100PK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


### Product data

| General Information         |                                          |
|-----------------------------|------------------------------------------|
| Cap-Base                    | G6.35                                    |
| Operating Position          | S90 [Standing +/-90D or Base Down (BDH)] |
| Life to 50% Failures (Nom)  | 50 hour(s)                               |
| Light Technical             |                                          |
| Color rendering index (CRI) | 100                                      |
| Operating and Electrical    |                                          |
| Power Consumption           | 50 W                                     |
| Voltage (Nom)               | 12 V                                     |
| Mechanical and Housing      |                                          |
| Bulb Material               | Quartz-UV Open                           |
| Net Weight (Piece)          | 0.004 lb                                 |

| Approval and Application        |                               |
|---------------------------------|-------------------------------|
| CE mark                         | Yes                           |
| Product Data                    |                               |
| Order product name              | 7027 50W G6.35 12V 1CT/10X10F |
| Full product name               | BRL 7027 50W 12V 100PK        |
| Full product code               | 871150040982950               |
| Order code                      | 316273                        |
| Material Nr. (12NC)             | 923870217103                  |
| Numerator - Quantity Per Pack   | 1                             |
| EAN/UPC - Product/Case          | 8711500409829                 |
| Numerator - Packs per outer box | 100                           |
| EAN/UPC - Case                  | 8711500423245                 |

# Halogen non-reflector

## Dimensional drawing



| Product    | D (max)  | L (min) | L (max) | L      | P (max) | P    | P (min) | C (max) |
|------------|----------|---------|---------|--------|---------|------|---------|---------|
| 7027 50W   | 1/2 inch | 1-3/16  | 1-1/4   | 1-3/16 | 1/16    | 1/16 | 1/16    | 1-3/4   |
| G6.35 12V  |          | inch    | inch    | inch   | inch    | inch | inch    | inch    |
| 1CT/10X10F |          |         |         |        |         |      |         |         |

