



Halogen non-reflector

6605 10W 6V 100PK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Luminous Flux	150 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	10 W
Voltage (Nom)	6 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open
Net Weight (Piece)	0.002 lb

Approval and Application	
CE mark	Yes
Product Data	
Order product name	6605 10W G4 6V 1CT/10X10F
Full product name	6605 10W 6V 100PK
Full product code	871150041009250
Order code	256842
Material Nr. (12NC)	923873910103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410092
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423320

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (max)	C (max)
6605 10W G4 6V 1CT/10X10F	3/8 inch	13/16 inch	1-1/4 inch

