



Plusline Compact

150 W R7s cap Clear Halogen linear lamp

Mains-voltage linear lamp giving white halogen light


Product data

General Information	
Cap-Base	R7s
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	2,400 lm
Luminous Efficacy (rated) (Nom)	16 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Lamp Current (Nom)	0.65 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3
Product Data	
Order product name	150 W R7s cap Clear Halogen linear lamp
Full product name	150 W R7s cap Clear Halogen linear lamp
Full product code	872790080887200
Order code	923919943202
Material Nr. (12NC)	923919943202
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.005 kg
EAN/UPC - Product/Case	8727900808872
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900808889

Plusline Compact

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
150 W R7s cap Clear Halogen linear lamp	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

