



Plusline Large

1500 W R7s cap Clear Halogen linear lamp

Mains-voltage linear lamp giving white halogen light


Product data

General Information	
Cap-Base	R7s
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	33,000 lm
Luminous Efficacy (rated) (Nom)	22 lm/W
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	1,500.0 W
Lamp Current (Nom)	6.52 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11
Approval and Application	
Energy Consumption kWh/1000 h	1500 kWh
Product Data	
Order product name	1500 W R7s cap Clear Halogen linear lamp
Full product name	1500 W R7s cap Clear Halogen linear lamp
Full product code	872790080857500
Order code	923932243241
Material Nr. (12NC)	923932243241
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.020 kg
EAN/UPC - Product/Case	8727900808575
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900808582

Plusline Large

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
1500 W R7s cap Clear Halogen linear lamp	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

