



Halogen non-reflector

EYB 82V 360W 24PK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

General Information	
Cap-Base	G5.3
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	75 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3300 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	360 W
Voltage (Nom)	82 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Net Weight (Piece)	0.02 lb
Product Data	
Order product name	14531 360W G5.3 82V 1CT
Full product name	EYB 82V 360W 24PK
Full product code	871150042463130
Order code	232579
Material Nr. (12NC)	924041528894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500424631
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500424648

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14531 360W	1/2 inch	1-1/4	1-1/4	1-1/4	1/16 inch	1/16	1/16	2-1/4
G5.3 82V		inch	inch	inch		inch	inch	inch
1CT								

