



Essential LV MR16

35 W GU5.3 cap Warm white Halogen spot

The Essential LV MR16 is part of the Philips "Value for Money" ranges. It is a good choice for professional end-users looking for high-quality accent light to create contrast in shops, hotels and restaurants.

Product data

General Information	
Cap-Base	GU5.3
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	430 lm

Operating and Electrical	
Power Consumption	35 W
Lamp Current (Nom)	2.92 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	MR16
Net Weight (Piece)	0.032 kg

Product Data	
Order product name	35 W GU5.3 cap Warm white Halogen spot
Full product name	35 W GU5.3 cap Warm white Halogen spot
Full product code	871150088593765
Order code	924049617186
Material Nr. (12NC)	924049617186
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500885937
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500886217

Essential LV MR16

Dimensional drawing



Product	D (max)	C (max)
35 W GU5.3 cap Warm white Halogen spot	51 mm	46 mm

