



Low Voltage Capsules

LV Capsule BC20W/T3/LAND/TP/12VCAPSULE 2PK

Functional light with substantial energy savings. Philips Halogen Low Voltage Capsules provide sparkling, white light. These lamps offer an average rated life of 2000 hours making them perfect for undercabinet or task lighting.

Warnings and Safety

- This lamp is pressurized and could shatter, so to avoid any injury and to avoid exposure to ultraviolet radiation, use only in fixtures that provide a protective shield of tempered glass.


Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	255 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	20 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T9
Product Data	
Order product name	20W G4 Sparkling light Dimmable Capsule
Full product name	LV Capsule BC20W/T3/LAND/TP/12VCAPSULE 2PK
Order code	417204
Material Nr. (12NC)	924062217123
Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.004 lb
EAN/UPC - Product/Case	046677417208
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677417203

Low Voltage Capsules

Dimensional drawing



Product	D (max)	L	C (max)
20W G4 Sparkling light Dimmable Capsule	7/16 inch	7/8 inch	1-5/16 inch

