



# Plusline ES Small

## Halogen 118MM 2Y 160W R7S 230V 1BC/10

Mains-voltage halogen linear lamp with superior quality and reliability. Offers very long lifetime and crisp halogen light. Ideal solution for decorative luminaires and for security or task lighting floodlights.

### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	3,100 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	19.4 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	160.0 W
Lamp Current (Nom)	0.70 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]
Approval and Application	
Energy Consumption kWh/1000 h	160 kWh
Product Data	
Order product name	Halogen 118MM 2Y 160W R7S 230V 1BC/10
Full product name	Halogen 118MM 2Y 160W R7S 230V 1BC/10
Full product code	872790092088800
Order code	924587544220
Material Nr. (12NC)	924587544220
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900920888
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900920895

Plusline ES Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Halogen 118MM 2Y 160W R7S 230V 1BC/10	11 mm	115.8 mm	114.2 mm	112.6 mm	118 mm

