



Halogen reflector

JCR 15V 150W H5 24 PACK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.


Product data

General Information	
Cap-Base	GZ6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	500 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3100 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	15 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Bulb Shape	R50
Net Weight (Piece)	0.055 lb
Product Data	
Order product name	JCR 15V 150W H5 24 PACK
Full product name	JCR 15V 150W H5 24 PACK
Full product code	871150041329130
Order code	249235
Material Nr. (12NC)	924793618594
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500413291
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500413307

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
JCR 15V 150W H5 24 PACK	2 inch	1-3/4 inch

