



Twistline GU10

BC35 TWISTLINE GU10/FL25 TP

Bright, white accent light with superior energy savings. Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.


Product data

General Information	
Cap-Base	GU10
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	20 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	35 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16
Product Data	
Order product name	35W GU10 Sparkling light Dimmable Mini-Reflector
Full product name	BC35 TWISTLINE GU10/FL25 TP
Order code	415737
Material Nr. (12NC)	924887136384
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.101 lb
EAN/UPC - Product/Case	046677415730
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677415735

Twistline GU10

Dimensional drawing



Product	D (max)	C (max)
35W GU10 Sparkling light Dimmable Mini-Reflector	2 inch	2-1/8 inch

