



DuraMax Fan

BC15C7C 120V 6/2 TP

Philips DuraMax® Long Life Fan Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in clear and white finishes adding a decorative touch to ceiling fan fixtures.

Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	105 lm
Operating and Electrical	
Power Consumption	15 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	C-7
Product Data	
Order product name	BC15C7C 120V 6/2 TP
Full product name	BC15C7C 120V 6/2 TP
Order code	133876
Material Nr. (12NC)	925172936306
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677133870
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677133875

DuraMax Fan

Dimensional drawing

Product

BC15C7C 120V 6/2 TP

