



# Halogen A19

## Halogen 29A19/EV/CL 120V 12/2

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar A-shape design. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	29 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Glass
Bulb Shape	A19
Product Data	
Order product name	29w (40w) Medium base (E26) A Shape
Full product name	Halogen 29A19/EV/CL 120V 12/2
Order code	410506
Material Nr. (12NC)	925702136301
Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.011 lb
EAN/UPC - Product/Case	046677410506
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677410501

# Halogen A19

## Dimensional drawing



Product	D	C (max)
29w (40w) Medium base (E26) A Shape	2.375 inch	4.13 inch

