



Reflector diam 63 mm

Refl 60W E27 230V NR63 30D FR 1CT/30

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63 [NR 63mm]
Product Data	
Order product name	Refl 60W E27 230V NR63 30D FR 1CT/30
Full product name	Refl 60W E27 230V NR63 30D FR 1CT/30
Full product code	871150004366578
Order code	926000005918
Material Nr. (12NC)	926000005918
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500043665
Numerator - Packs per outer box	30
EAN/UPC - Case	8711500343994


Reflector diam 63 mm

Dimensional drawing



Product	D
Ref 60W E27 230V NR63 30D FR 1CT/30	63 mm

Photometric data



Light Distribution Diagram - Ref 60W E27 230V NR63 30D FR 1CT/30

