



Reflector diam 63 mm

40 W Frosted E27 cap Incandescent lamp

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63
Product Data	
Order product name	40 W Frosted E27 cap Incandescent lamp
Full product name	40 W Frosted E27 cap Incandescent lamp
Full product code	871150004360378
Order code	926000006213
Material Nr. (12NC)	926000006213
Numerator - Quantity Per Pack	1
Net Weight (Piece)	25.970 g
EAN/UPC - Product/Case	8711500043603
Numerator - Packs per outer box	30
EAN/UPC - Case	8711500343956

Reflector diam 63 mm

Dimensional drawing



Product	D
40 W Frosted E27 cap Incandescent lamp	63 mm

