



T8 Standard

F25T8/TL835/ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL835 [CCT of 3500K (835)]
Luminous Flux	2,150 lm
Color Designation	TL835
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	25 W
Mechanical and Housing	
Bulb Shape	T-8
Net Weight (Piece)	0.225 lb

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F25T8/TL835/ALTO 30PK
Full product name	F25T8/TL835/ALTO 30PK
Order code	281907
Material Nr. (12NC)	927851083503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281908
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677281903

T8 Standard

Dimensional drawing

Product
F25T8/TL835/ALTO 30PK

