



T8 Plus

F32T8/TL850 PLUS ALTO HV 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® Plus
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux	2,850 lm
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	32 W
Mechanical and Housing	
Bulb Shape	T-8
Net Weight (Piece)	0.3 lb

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F32T8/TL850 PLUS ALTO HV 30PK
Full product name	F32T8/TL850 PLUS ALTO HV 30PK
Order code	281816
Material Nr. (12NC)	927852085002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281816
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677281811

T8 Plus

Dimensional drawing

Product
F32T8/TL850 PLUS ALTO HV 30PK

