



U-Bent Rapid Start T8

FB32T8/TL841/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	2,800 lm
Color Designation	TL841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	32 W
Mechanical and Housing	
Bulb Shape	T8-6U [U-bent T 8/8 inch with 6" spacing]
Net Weight (Piece)	0.002 lb

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB32T8/TL841/6 ALTO 20PK
Full product name	FB32T8/TL841/6 ALTO 20PK
Order code	379024
Material Nr. (12NC)	927860084102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677379025
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677379020

U-Bent Rapid Start T8

Dimensional drawing

Product
FB32T8/TL841/6 ALTO 20PK

