



Rapid Start T8

F40T8/TL841 ALTO 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	3,775 lm
Color Designation	TL841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	86
Operating and Electrical	
Power Consumption	40 W
Mechanical and Housing	
Bulb Shape	T-8
Net Weight (Piece)	0.428 lb

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F40T8/TL841 ALTO 25PK
Full product name	F40T8/TL841 ALTO 25PK
Order code	368472
Material Nr. (12NC)	927870584101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677368470
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677368475

Rapid Start T8

Dimensional drawing

Product
F40T8/TL841 ALTO 25PK

