



Tuff Guard High CRI T8 Lamps

F32T8/TL935/ALTO TG 30PK

Tuff Guard T8 lamps are designed to contain shattered glass particles in case of accidental breakage. Coated lighting is essential to help ensure the welfare of your customers, employees, and operation.

Warnings and Safety

- The lamps must be installed and operating in ambient temperatures below 120°F.
- The lamps cannot be used in fixtures employing defective ballasts, ballasts that have been used longer than their rated life or ballasts that are improperly wired.
- The lamps cannot be used in fixtures where poor pin contact occurs.
- Lamp types and ballast types must be compatible (rapid start lamps with rapid start ballast, etc.).
- Lamps are recommended for open fixtures.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	935 [CCT of 3500K]
Beam Angle (Nom)	0 degree(s)
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	>90
Operating and Electrical	
Lamp Current (Nom)	265 mA
Wattage Equivalent	32 W

Voltage (Nom)	137 V
Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Shape	T-8
Net Weight (Piece)	0.001 kg
Approval and Application	
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F32T8/TL935/ALTO TG 30PK
Full product name	F32T8/TL935/ALTO TG 30PK
Order code	927871204905

Tuff Guard High CRI T8 Lamps

Material Nr. (12NC)	927871204905
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677536497
Numerator - Packs per outer box	30

EAN/UPC - Case	50046677536492
----------------	----------------

Dimensional drawing

Product	C (max)	D (max)
F32T8/TL935/ALTO TG 30PK	1,213.6 mm	27.9 mm

