



PLUS T8 High Output

F96T8/TL850/PLUS/HO/ALTO 25/1

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Product data

General Information	
Cap-Base	R17d (RDC)
Features	ALTO® Plus
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux	8,100 lm
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	86 W
Mechanical and Housing	
Bulb Shape	T-8
Net Weight (Piece)	0.341 kg

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F96T8/TL850/PLUS/HO/ALTO 25/1
Full product name	F96T8/TL850/PLUS/HO/ALTO 25/1
Order code	236893
Material Nr. (12NC)	927874085005
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677236892
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677236897

PLUS T8 High Output

Dimensional drawing

Product
F96T8/TL850/PLUS/HO/ALTO 25/1

