



Retail Sales T12

F14T12/SOFT WHITE/15 6PK

High Performance, Long Life, Environmentally-Responsible Lamps. These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Light Technical	
Color Code	Ultralume 30 [CCT of 3000K (830)]
Luminous Flux	700 lm
Color Designation	Ultralume 30
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	14 W
Mechanical and Housing	
Bulb Shape	T-12

Net Weight (Piece)	0.001 kg
Product Data	
Order product name	14W T12 Soft White Tubular Fluorescent
Full product name	F14T12/SOFT WHITE/15 6PK
Order code	141507
Material Nr. (12NC)	927881083003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677141509
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677141504

Retail Sales T12

Dimensional drawing

Product

14W T12 Soft White Tubular Fluorescent

