



Preheat T12

F20T12/D ALTO 30PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Light Technical	
Color Code	54-765
Luminous Flux	1,075 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	73
Operating and Electrical	
Power Consumption	20 W
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.113 kg

Approval and Application	
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F20T12/D ALTO 30PK
Full product name	F20T12/D ALTO 30PK
Order code	273284
Material Nr. (12NC)	927883005405
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677273286
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677273281

Preheat T12

Dimensional drawing

Product
F20T12/D ALTO 30PK

