



Retail Sales T12

F20T12/SPEC35 UPC 30PK

High Performance, Long Life, Environmentally-Responsible Lamps. These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Light Technical	
Color Code	SPEC35 [CCT of 3500K (735)]
Luminous Flux	1,275 lm
Color Designation	SPEC35
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	73
Operating and Electrical	
Power Consumption	20 W
Mechanical and Housing	
Bulb Shape	T-12

Approval and Application	
Mercury (Hg) Content (Nom)	16.0 mg
Product Data	
Order product name	20W T12 Neutral Tubular Fluorescent
Full product name	F20T12/SPEC35 UPC 30PK
Order code	386938
Material Nr. (12NC)	927883073504
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.002 lb
EAN/UPC - Product/Case	046677386931
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677386936

Dimensional drawing

Product
20W T12 Neutral Tubular Fluorescent

