



TuffGuard Coated T12

F40T12/CWSupreme/ALTO TG

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T-12
Features	ALTO® (ALTO)	Net Weight (Piece)	0.002 lb
Light Technical		Approval and Application	
Luminous Flux	2,600 lm	Energy Saving Product	Energy Saving
Color Designation	Cool White Supreme	Mercury (Hg) Content (Nom)	4.4 mg
Correlated Color Temperature (Nom)	4100 K		
Color rendering index (CRI)	89		
Operating and Electrical		Product Data	
Power Consumption	40 W	Order product name	F40T12/CWSupreme/ALTO TG
		Full product name	F40T12/CWSupreme/ALTO TG
		Order code	424002
		Material Nr. (12NC)	927887803902

TuffGuard Coated T12

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677424008
Numerator - Packs per outer box	30

EAN/UPC - Case	50046677424003
----------------	----------------

Dimensional drawing

Product
F40T12/CWSupreme/ALTO TG

