

High Output T12

F72T12/CW/HO ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	R17d (RDC)
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	6,350 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	85 W
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.739 lb

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	F72T12/CW/HO ALTO 15PK
Full product name	F72T12/CW/HO ALTO 15PK
Order code	366518
Material Nr. (12NC)	927893203304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677366513
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677366518

High Output T12

Dimensional drawing

Product
F72T12/CW/HO ALTO 15PK



T12 Recessed Double Contact

