



High CRI T12

F96T12/C50Supreme/ALTO 15pk

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	FA8
Features	ALTO® (ALTO)
Light Technical	
Luminous Flux	5,000 lm
Color Designation	C50 Supreme
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	90
Operating and Electrical	
Power Consumption	75 W
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.974 lb

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	F96T12/C50Supreme/ALTO 15pk
Full product name	F96T12/C50Supreme/ALTO 15pk
Order code	423871
Material Nr. (12NC)	927895000211
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677423872
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677423877

High CRI T12

Dimensional drawing

Product
F96T12/C50Supreme/ALTO 15pk

