



PL-S Blacklight Blue

LEAD FREE PL-S 9W/08 60PK

PL-S Blacklight Blue is a special low-wattage compact fluorescent lamp emitting long wave UV radiation for detection and analysis purposes in archaeology, money checking, forensic science, food industry, medicine, mineralogy, philately as well for special effects in night clubs, discos, theatres and sign lighting. The 2-pin version is designed for operation on electromagnetic gear, the 4-pin version is designed for operation on electronic gear. Both versions are provided with a plug-in/pull-out lamp base.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Voltage (Nom)		60 V
Cap-Base	G23			
Useful Life (Nom)	3.000 hour(s)			
Light Technical		Mechanical and Housing		
Color Code	108 [08 lead free glass]	Bulb Shape	2XT12	
Color Designation	Blacklight Blue	Net Weight (Piece)	0.071 lb	
Operating and Electrical		Approval and Application		
Power Consumption	8.6 W	Mercury (Hg) Content (Nom)	3.0 mg	
Lamp Current (Nom)	0.17 A	CE mark	Yes	

PL-S Blacklight Blue

UV	
UV-A Radiation 100Hr (IEC)	1.65 W
Product Data	
Order product name	PL-S 9W BLB/2P 1CT/6X10CC
Full product name	LEAD FREE PL-S 9W/08 60PK
Full product code	871150095090180
Order code	157529

Material Nr. (12NC)	927901710807
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500950901
Numerator - Packs per outer box	60
EAN/UPC - Case	8711500950925

Dimensional drawing



Product	D1 (max)	B (max)
PL-S 9W BLB/2P 1CT/6X10CC	9/16 inch	5-3/4 inch

