

PHILIPS

Lighting



PL-L Long 4-Pin Base

PL-L 18W/835/4P 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

General Information

Cap-Base	2G11
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical

Color Code	835 [CCT of 3500K]
Luminous Flux	1,200 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color rendering index (CRI)	82

Operating and Electrical

Power Consumption	18.0 W
Lamp Current (Nom)	0.375 A
Voltage (Nom)	58 V

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing


Bulb Finish	Silicon
Net Weight (Piece)	60.900 g

Product Data

Order product name	PL-L 18W/835/4P 1CT/25
Full product name	PL-L 18W/835/4P 1CT/25
Order code	359323
Material Nr. (12NC)	927903183521
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677359324
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677359329


PL-L Long 4-Pin Base

Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-L 18W/835/4P 1CT/25	39.0 mm	18.0 mm	226.6 mm

Photometric data



Spectral Power Distribution Colour - PL-L 18W/835/4P 1CT/25

