



PL-L Long 4-Pin Base

PL-L 36W/835/4P 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	2G11
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	2,900 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	36.0 W
Lamp Current (Nom)	0.435 A

Voltage (Nom)	106 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Silicon
Net Weight (Piece)	0.229 lb
Product Data	
Order product name	PL-L 36W/835/4P 1CT/25
Full product name	PL-L 36W/835/4P 1CT/25
Order code	349423
Material Nr. (12NC)	927904583521
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677349424

PL-L Long 4-Pin Base


Numerator - Packs per outer box	25
EAN/UPC - Case	50046677349429

Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-L 36W/835/4P 1CT/25	1-9/16 inch	3/4 inch	16-7/16 inch

Photometric data



Spectral Power Distribution Colour - PL-L 36W/835/4P 1CT/25

