



MASTER PL-C 4 Pin

26 W 4 Pin Cool white Non integrated compact fluorescent

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	G24q-3		82
Nominal lifetime	10,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	26.0 W
Luminous Flux	1,800 lm	Lamp Current (Nom)	0.335 A
Luminous Efficacy (rated) (Nom)	67 lm/W		
Color Designation	Cool White (CW)	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	Yes

MASTER PL-C 4 Pin

Approval and Application


Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	29 kWh

Product Data

Order product name	26 W 4 Pin Cool white Non integrated compact fluorescent
Full product name	26 W 4 Pin Cool white Non integrated compact fluorescent
Full product code	871150062336200


Order code	927907384002
Material Nr. (12NC)	927907384002
Numerator - Quantity Per Pack	1
Net Weight (Piece)	60.400 g
EAN/UPC - Product/Case	8711500623362
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500716057

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
26 W 4 Pin Cool white Non integrated compact fluorescent	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-C 26W/840/4P 1CT/5X10BOX


MASTER PL-C 4 Pin

Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - MASTER PL-C 26W/840/4P 1CT/5X10BOX

