



MASTER PL-L 4 Pin 4-針腳型

55 W 4 Pin Cool white Non integrated compact fluorescent

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 2 個平行螢光燈管

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊		燈具電流 (標稱)		0.525 A
燈座基底	2G11			
標稱使用壽命	15,000 h			
照明技術				
色碼	840 [CCT of 4000K]			
光通量	4,800 lm			
色彩名稱	冷白光 (CW)			
光效 (額定) (標準)	87 lm/W			
相關色彩溫度 (規範)	4000 K			
演色性指數 (CRI)	82			
運轉與電力				
耗電量	55.0 W			


控制與調光	
可調光	是
認證與應用	
汞 (Hg) 含量 (標稱)	2.0 mg
能源消耗 kWh/1000 h	61 kWh
產品資料	
下訂產品名稱	55 W 4 Pin Cool white Non integrated compact fluorescent
完整產品名稱	55 W 4 Pin Cool white Non integrated compact fluorescent
完整產品代碼	871150061542841
訂單代碼	927908708472

MASTER PL-L 4 Pin 4-針腳型

材質 Nr. (12NC)	927908708472
分子 - 每個包裝的數量	1
淨重 (個)	134.000 g
EAN/UPC - 產品/案例	8711500615428


分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500615527

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
55 W 4 Pin Cool white Non integrated compact fluorescent	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

光度数据



Spectral Power Distribution Colour - MASTER PL-L 55W/840/4P 1CT/25

