



PL-T Triple 4-Pin Base

PL-T 42W/841/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	GX24q-4
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	3,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (Rated) (Min)	80 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	38.0 W


Lamp Current (Nom)	0.320 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	0.183 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 42W/841/A/4P 1CT/5X10BOX ALTO
Full product name	PL-T 42W/841/A/4P 1CT/5X10BOX ALTO

PL-T Triple 4-Pin Base

Order code	149039
Material Nr. (12NC)	927911484120
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677149031



Numerator - Packs per outer box	10
EAN/UPC - Case	50046677149036

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 42W/841/A/4P 1CT/5X10BOX ALTO	1-5/8 inch	4-3/4 inch	5-3/4 inch	6-3/8 inch

Lifetime



Lumen Maintenance Diagram - PL-T 42W/841/A/4P 1CT/5X10BOX ALTO

Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

PL-T Triple 4-Pin Base

