



# TL5 Essential HE Super 80

## 28 W G5 Cool daylight Linear fluorescent tube

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

### Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


### Product data

General Information		Controls and Dimming	
Cap-Base	G5	Dimmable	No
Nominal lifetime	15,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	865 [CCT of 6500K]	Bulb Shape	T5
Luminous Flux	2,700 lm		
Luminous Efficacy (rated) (Nom)	94 lm/W	Approval and Application	
Color Designation	Cool Daylight	Mercury (Hg) Content (Nom)	2.0 mg
Correlated Color Temperature (Nom)	6500 K	Energy Consumption kWh/1000 h	31 kWh
Color rendering index (CRI)	82		
Operating and Electrical		Product Data	
Power Consumption	27.8 W	Order product name	28 W G5 Cool daylight Linear fluorescent tube
Lamp Current (Nom)	0.170 A	Full product name	28 W G5 Cool daylight Linear fluorescent tube
		Full product code	871150057047555
		Order code	927926786558
		Material Nr. (12NC)	927926786558
		Numerator - Quantity Per Pack	1
		Net Weight (Piece)	88.500 g

# TL5 Essential HE Super 80


EAN/UPC - Product/Case	8711500570475
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500570482

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
28 W G5 Cool daylight Linear fluorescent tube	17.0 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

## Photometric data



Spectral Power Distribution Colour - TL5 Essential 28W/865 1SL/40

