

# PHILIPS

Circular fluorescent

Master T5

22 W

Cool white

927965084013



## Slim design for a bright and stylish home

Choose Philips T5s for a slim design that can be used in different applications to create a stylish home atmosphere. Their Super 80 Color technology gives superior light quality that enhances any decor.

### **Saves energy**

- Saves energy

### **For stylish modern fittings**

- For a bright and stylish home with slim design

### **Gives you bright light**

- Vibrant experience with extra brightness

### **High efficacy with high lumen output**

- High initial light output

# Highlights

## Saves energy

### Slim essential

Provides home users with aesthetic miniaturized lighting solution with high reliability

## Bright boost

High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

## High initial light output

High Light output provides better light quality with more brightness and allows more vibrance in home application.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Socket: 2GX13

## Bulb dimensions

- Height: 230 mm
- Width: 18 mm

## Durability

- Nominal lifetime: 12,000 hour(s)

## Light characteristics

- Color rendering index (CRI): 81
- Color temperature: 4000 K
- Light Color Category: Cool White
- Nominal luminous flux: 1800 lumen
- Correlated Color Temperature (Nom): 4000 K
- Luminous Efficacy (rated) (Nom): 82 lm/W
- Luminous Flux: 1,800 lumen

## Power consumption

- Wattage: 23.5 W
- Energy Efficiency Class: G
- Power Consumption: 23.5 W

## Technical specifications

- Light output: 1,800 lumen
- Shape: Circular fluorescent
- Chromaticity Coordinate Y: 0.38
- Chromaticity Coordinate X: 0.38
- EPREL Registration Number: 423619
- Flux measurement reference: Sphere
- Dimmable: Yes
- Cap-Base: 2GX13 | 2GX13

## Packaging dimensions and weight

- EAN/UPC - product: 8711500642219
- Net weight: 80.000 g
- Gross weight: 107.300 g
- Height: 2.500 cm
- Length: 25.500 cm
- Width: 24.000 cm
- Material number (12NC): 927965084013



Issue date: 2023-11-08  
Version: 0.668

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)