



TL-D LIFEMAX Super 80

36 W G13 Incandescent white Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	36 W G13 Incandescent white Linear fluorescent tube
Full product name	36 W G13 Incandescent white Linear fluorescent tube
Full product code	871150028584340
Order code	927982282736
Material Nr. (12NC)	927982282736
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.140 kg
EAN/UPC - Product/Case	8711500285843
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500285850



TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
36 W G13 Incandescent white	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
Linear fluorescent tube					

Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - TL-D 36W/827 1SL/25

