



TL-D LIFEMAX Super 80

36 W G13 Incandescent white Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.


Product data

Informasi Umum	
Tutup-Dasar	G13 [Medium Bi-Pin Fluorescent]
Nominal masa pakai	15.000 jam
Masa Pakai hingga 50 % Kegagalan (Nom)	15.000 jam
Teknis Lampu	
Kode Warna	827 [CCT of 2700K]
Penandaan Warna	Lampu-pijar Putih
Daya Penerangan (terukur) (Nom)	90 lm/W
Suhu Warna Terkorelasi (Nom)	2700 K
Indeks renderasi warna (CRI)	82
Pengoperasian dan Kelistrikan	
Konsumsi Daya	36 W
Arus Lampu (Nom)	0,440 A
Tegangan (Nom)	103 V
Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Bentuk Bohlam	T8
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	2,0 mg
Data Produk	
Nama produk pesanan	36 W G13 Incandescent white Linear fluorescent tube
Nama lengkap produk	36 W G13 Incandescent white Linear fluorescent tube
Kode produk lengkap	871150028584340
Kode urutan	927982282736
No. Material (12NC)	927982282736
Numerator - Jumlah Per Pak	1
Berat Bersih (Bagian)	0,140 kg
EAN/UPC - Produk/Kantung	8711500285843
Numerator - Pak per kotak bagian luar	25
EAN/UPC - Kantung	8711500285850



TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
36 W G13 Incandescent white	28 mm	1.199,4 mm	1.206,5 mm	1.204,1 mm	1.213,6 mm
Linear fluorescent tube					

Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - TL-D 36W/827 1SL/25

