



# TL-D LIFEMAX Super 80

## 36 W G13 Cool white Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Product data

Informasi Umum	
Tutup-Dasar	G13 [Medium Bi-Pin Fluorescent]
Nominal masa pakai	15.000 jam
Masa Pakai hingga 50 % Kegagalan (Nom)	15.000 jam

Teknis Lampu	
Kode Warna	840 [CCT of 4000K]
Penandaan Warna	Cool White (CW)
Suhu Warna Terkorelasi (Nom)	4000 K
Daya Penerangan (terukur) (Nom)	90 lm/W
Indeks renderasi warna (CRI)	82

Pengoperasian dan Kelistrikan	
Konsumsi Daya	36 W
Arus Lampu (Nom)	0,440 A
Tegangan (Nom)	103 V

Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Bentuk Bohlam	T8
Berat Bersih (Bagian)	0,140 kg

Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	2,0 mg

Data Produk	
Nama produk pesanan	36 W G13 Cool white Linear fluorescent tube
Nama lengkap produk	36 W G13 Cool white Linear fluorescent tube
Kode produk lengkap	871150028561440
Kode urutan	927982284036
No. Material (12NC)	927982284036
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500285614
Numerator - Pak per kotak bagian luar	25
EAN/UPC - Kantung	8711500285898



# TL-D LIFEMAX Super 80

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
36 W G13 Cool white Linear fluorescent tube	28 mm	1.199,4 mm	1.206,5 mm	1.204,1 mm	1.213,6 mm

## Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - TL-D 36W/840 1SL/25

## TL-D LIFEMAX Super 80

