



T5 Standard

F14T5/835/ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G5
Features	HE Alto® [High Efficiency Alto]
Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	1,350 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	14.0 W
Lamp Current (Nom)	0.165 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	0.119 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	14W/835 Min Bipin T5 HE ALTO UNP/40
Full product name	F14T5/835/ALTO 40PK
Order code	230797
Material Nr. (12NC)	927990483522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677230791
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677230796


T5 Standard

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
14W/835 Min Bipin T5	11/16 inch	21-5/8 inch	21-15/16 inch	21-13/16 inch	22-3/16 inch
HE ALTO UNP/40					

Photometric data




Spectral Power Distribution Colour - 14W/835 Min Bipin T5 HE ALTO UNP/40

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

T5 Standard

Lifetime



Lumen Maintenance Diagram - 14W/835 Min Bipin T5 HE ALTO UNP/40

