



T5 Standard

F14T5/841/ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G5
Features	HE Alto® [High Efficiency Alto]
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	1,350 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	14.0 W
Lamp Current (Nom)	0.165 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	0.119 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	14W/841 Min Bipin T5 HE ALTO UNP/40
Full product name	F14T5/841/ALTO 40PK
Order code	230805
Material Nr. (12NC)	927990484022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677230807
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677230802



T5 Standard

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
14W/841 Min Bipin T5	11/16 inch	21-5/8 inch	21-15/16 inch	21-13/16 inch	22-3/16 inch
HE ALTO UNP/40					

Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - 14W/841 Min Bipin T5 HE ALTO UNP/40

T5 Standard

