



T5 High Output

F24T5/830/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G5
Features	HO Alto® [High Output Alto]
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,950 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	76 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	22.5 W
Lamp Current (Nom)	0.295 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	0.119 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	F24T5/830/HO/ALTO 40PK
Full product name	F24T5/830/HO/ALTO 40PK
Order code	290197
Material Nr. (12NC)	927992183022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677290191
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677290196


T5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F24T5/830/HO/ALTO 40PK	11/16 inch	21-5/8 inch	21-15/16 inch	21-13/16 inch	22-3/16 inch

Photometric data




Spectral Power Distribution Colour - F24T5/830/HO/ALTO 40PK

Lifetime



Life expectancy diagram - 3 hour cycle



Lumen Maintenance Diagram - F24T5/830/HO/ALTO 40PK

T5 High Output

Lifetime

Life expectancy diagram - 12 hour cycle

