



T5 High Output

F24T5/835/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G5
Features	HO Alto® [High Output Alto]
Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	1,950 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	76 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	22.5 W
Lamp Current (Nom)	0.295 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	0.119 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	24W/835 Min Bipin T5 HO ALTO UNP
Full product name	F24T5/835/HO/ALTO 40PK
Order code	290205
Material Nr. (12NC)	927992183522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677290207
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677290202


T5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
24W/835 Min Bipin T5	11/16 inch	21-5/8 inch	21-15/16 inch	21-13/16 inch	22-3/16 inch
HO ALTO UNP					

Photometric data




Spectral Power Distribution Colour - 24W/835 Min Bipin T5 HO ALTO UNP

Lifetime



Life expectancy diagram - 3 hour cycle



Lumen Maintenance Diagram - 24W/835 Min Bipin T5 HO ALTO UNP

T5 High Output

Lifetime

Life expectancy diagram - 12 hour cycle

